

## AquaT Super Compact

SMALLER & LIGHTER MARINE TOILET

AquaT Super Compact - the smallest and lightest toilet in our AquaT range, designed for making a water toilet installation possible onboard even smaller vessels, requiring less packaging space than ever before.



### Soft close

Prevents noise




### More space

50 mm smaller than the compact model




### Features & Benefits

- Smallest and lightest in our AquaT marine toilet range
- Reversible pump mounting on manual model, left to right
- Soft close plastic seat on white vitreous porcelain
- All corrosion resistant and easy to maintain
- Available in two versions, manual and electric (12V)
- Clean lines - attractive design
- Hygienic, easy-to-clean
- Low water consumption. 2,5 l/flush
- Versatile plumbing connection options
- Designed for virtually any onboard mounting position
- Built-in check valve
- May be installed above or below the waterline
- Suitable for OEM or replacement installation
- Corrosion resistant materials throughout
- Long Service life
- Complies with ISO 8846, ignition protection and EN 55014 EMC



Toilet mounted below the waterline and discharging overboard.




Toilet mounted above the waterline and discharging overboard.

### Dimensions

#### AquaT MANUAL - TOILET

Part. nr.	Description	Net weight		A	B	C	D	E	F	mm/
										inch
80-47625-01	AquaT Toilet Manual Super Compact	8,5	kg	340	605	300	400	215	460	mm
		19	lbs	13,39	23,82	11,81	15,75	8,46	18,11	inch



#### AquaT STANDARD ELECTRIC - TOILET

Part No.	Description	Net weight		A	B	C	D	E	mm/
									inch
80-47626-01	AquaT Standard Electric Super Compact, 12V	9,2	kg	340	635	330	450	215	mm
		20	lbs	13,39	25,00	12,99	17,72	8,46	inch

