

Viking Compact

FULL-CAPACITY, HAND-POWERED BILGE PUMP

When you need to bail water from the bilge at sea, you need to be able to rely on the pump at hand. Thanks to the Viking Compact manual bilge pump's well considered design, bailing has never been easier. Perfect for installation in tight spaces, the Viking Compact can be mounted wherever it's most appropriate.

Discover the Viking Compact manual bilge pump, combining the best aspects of simplicity, reliability and modern industrial design.

This rugged, yet sleekly designed, single-chamber diaphragm pump provides first-rate performance and is a snap to install. It can be fitted in minutes from one side of the bulkhead with just four screws, self-sealing against the surface with a durable, watertight gasket.

With the pump house recessed behind the bulkhead, only the handle is visible from the cabin or cockpit. The well-proven diaphragm design provides high pumping capacity, ensures easy pumping action and complies with ISO 15083 safety requirements.

The Viking Compact's inlet and outlet ports can be swiveled 360° and are delivered in two sizes with every pump, Ø25mm (1") and Ø38mm (1½"). Naturally, the Viking Compact has KlickTite™ connectors fitted as standard, literally making hose connections a snap!



Dependability in the grasp of your hand!

Features & Benefits

- Quick to install from one side of the bulkhead
- Fits industry standard aperture, even in tight spaces
- Robust pump handle and cover in-one
- Self-priming for immediate effect
- 3.3 meter (10'8") combined lift/head
- Easy, low-cost, low-frequency maintenance
- Durable gasket for tight fit against the bulkhead
- Rattle-free design
- Polypropylene body
- All metal parts made of stainless steel
- Easy pump-action, single diaphragm design
- KlickTite™ port connectors standard
- Hose connectors can be turned in any direction
- Heavy duty non-choke valves throughout
- High flow tricuspid valve on the outlet port
- Complies with ISO 15083

Technical specifications and capacity data

Body	Polypropylene
Cover	ABS
Diaphragm	Nitrile rubber
Valves	Nitrile rubber (1 leaf and 1 tricuspid valve)
Wetted parts	Polypropylene, PA66GF30 plastics and nitrile rubber
Maximum lift	2.1 meters (7 feet)
Maximum head	1.2 meters (4 feet)
Combined head/lift	3.3 meters (10.8 feet)
Connection	KlickTite™ connectors for 1" (25mm) or 1 1/2" (38mm) hose; both options included
Max. liquid temp	+60°C (140°F)
Weight	0.675 kg (1.5 pounds)

Flow at 10 kPa head and 45 strokes/min

Ø25mm connections	34,5 liters/minute (9.1 US gallons/minute)
Ø38mm connections	45 liters/minute (11.9 US gallons/minute)



PART NO.	PART NO. US	DESCRIPTION
10-24800-01	10-24800-01	VIKING COMPACT W. DIA. 25 MM (1") AND DIA. 38 MM (1 1/2") PORTS